

1023303010

EMCG-1

Microphone for Network Loudspeakers

 Automatic Volume



DESCRIPTION

- Cable gland with integrated electret microphone for Exigo Network Loudspeakers
- Listen in to any IP speaker
- Adjust output volume automatically according to the ambient noise level

SPECIFICATIONS

GENERAL

Size	M20
Weight	15g
Color	Light grey RAL 7035
IP grade	IP66
Operating temperature range	-40° to 70° C / -40° to 158 ° F
Storage temperature range	-40° to 70° C / -40° to 158 ° F
Relative humidity	< 95% not condensing
EMC	CE and FCC Part 15

USED WITH

1023301310

ELSII-10H

Network Horn Loudspeaker, 10W, Ethernet

