

## Product data sheet

### Characteristics

# 8538SCASP3

NEMA Combination Starter, Type S, 30A fusible disconnect, Size 1, 27A, melting alloy overload, 120 VAC coil, NEMA 3R/12

Product availability : Stock - Normally stocked in distribution facility



Price\* : 3,615.00 USD



### Main

Product	Combination Starter
Type	S
Control Circuit Type	Separate control circuit

### Complementary

Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Starter Type	Non reversing
Line Rated Current	27 A
Number of Poles	3P
Horsepower Rating	10 hp 460 V AC, 3 phase 10 hp 575 V AC, 3 phase
Maximum Voltage Rating	600 V AC
Control Units	Selector switch HAND-OFF-AUTO)
Pilot Light	Red indicator on LED Green indicator off LED
Auxiliary Contacts	2 NO + 2 NC
Thermal overload type	Melting alloy 3
Disconnect Type	Fusible disconnect switch H and K, 30 A, electrical SPDT
NEMA size	1
Height	24 in (609.60 mm)
Depth	8.34 in (211.84 mm)
Width	9.5 in (241.30 mm)
Handle Swing	3.25 in (82.55 mm)

\* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Apr 28, 2021

## Environment

Enclosure Type	NEMA 12 painted sheet steel with external reset
Product certifications	CSA UL Listed

## Ordering and shipping details

Category	21213 - 8538,39 SC,SD(NOT S*R,T,W)
Discount Schedule	CP1
GTIN	00785901828457
Nbr. of units in pkg.	1
Package weight(Lbs)	39.43 lb(US) (17.89 kg)
Returnability	Yes
Country of origin	MX

## Packing Units

Package 1 Height	10.70 in (27.178 cm)
Package 1 width	13.00 in (33.020 cm)
Package 1 Length	29.00 in (73.660 cm)

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Not compliant
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.

## Contractual warranty

Warranty	18 months
----------	-----------