


Product data sheet

Specifications



Contactor, Type L, multipole lighting, mechanically held, 30A, 12 pole, 600 V, 110/120 VAC 50/60 Hz coil, open style

8903LXO1200V02

Product availability : Stock - Normally stocked in distribution facility

Price* : 1,466.00 USD

Main

Product or Component Type	Mechanically Held Lighting Contactor
Range of Product	8903LX
Control Circuit	Separate control circuit

Complementary

Control Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Inrush power in VA	180 VA 60 Hz 170 VA 50 Hz 180 VA 50/60 Hz
Current Rating	20 A tungsten 30 A fluorescent
Number of Poles	12P 12 NO
Control Unit	No control units
Pilot Light	No indicator
Other Options	None
Electrical Connection	Screw-clamp terminals
Height	8.82 in (224 mm)
Depth	3.27 in (83 mm)
Width	5.63 in (143 mm)

Environment

Enclosure Type	Not rated (open device)
Product Certifications	UL Listed CSA

Ordering and shipping details

Category	21322-8903 LX (NOT L)
Discount Schedule	CP1
GTIN	785901057468
Number of Units in Package 1	1

* Price is “List Price” and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 1 Weight	5.93 lb(US) (2.69 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	4.41 in (11.2 cm)
Package 1 Width	7.40 in (18.8 cm)
Package 1 Length	10.51 in (26.7 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
PVC free	Yes
Halogen content performance	Halogen free plastic parts product

Contractual warranty

Warranty	18 months
----------	-----------