

Product data sheet

Characteristics

9422TDF63

Operating mechanism, flange mounted, variable depth, 60A, 600 V, H, K, J, R fuseholder, switch mechanism

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 569.00 USD



Main

Range	9422T
Product	Disconnect Switch
Disconnect Type	Fusible disconnect switch

Complementary

Mounting Type	Flange rod variable depth
Current Rating	60 A
Horsepower Rating	15 hp 200 V AC 15 hp 230 V AC 30 hp 460 V AC 50 hp 575 V AC 10 hp 250 V DC
Fuse Rating	60 A 600 V
Handle Type	Ordered separately
Fuse Type	J H K R

Environment

Certifications	UL Recognized CSA
----------------	----------------------

Ordering and shipping details

Category	21732 - 9422
----------	--------------

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

May 25, 2021

Discount Schedule	CP1
GTIN	00785901879879
Nbr. of units in pkg.	1
Package weight(Lbs)	6.21 lb(US) (2.82 kg)
Returnability	No
Country of origin	MX

Packing Units

Package 1 Height	7.10 in (18.034 cm)
Package 1 width	11.20 in (28.448 cm)
Package 1 Length	16.00 in (40.640 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)

Contractual warranty

Warranty	18 months
----------	-----------