

# Product data sheet

Specifications



## Rack PDU, Basic, Zero U, 30A, 200/208V, (20)C13 & (4)C19

AP7541

Product availability : Stock - Normally stocked in distribution facility

### Overview

Presentation	APC Basic Rack PDUs distribute reliable rack power distribution via a single input with multiple output receptacles. Easily mount this vertical PDU in racks or enclosures. It occupies zero U of valuable rack space, which allows space for more equipment in the rack. This vertical PDU does not require additional tools to mount into APC NetShelter Enclosures. Enables a quick recovery from overload events. Packaging Includes PDU, Installation guide, Rack Mounting brackets, Toolless Mounting Kit.
Lead time	Usually in Stock

### Main

Main Input Voltage	200 V 208 V 230 V
Main Output Voltage	200 V 208 V
Plug standard	NEMA L6-30P
Number of rack unit	0U
Cable length	10 ft (3.05 m)
Number of cables	1
Provided Equipment	Installation guide Rack Mounting brackets Toolless Mounting Kit

### Physical

Color	Black
Height	63.74 in (161.9 cm)
Width	2.20 in (5.6 cm)
Depth	1.73 in (4.4 cm)
Net Weight	12.28 lb(US) (5.57 kg)
Mounting Location	Side
Mounting preference	No preference
Mounting Mode	Rack-mounted
USB compatible	No

### Input

Line Rated Current	24 A
Input current limits	30 A

Load Capacity	4992 VA
Input Frequency	50/60 Hz

### Output

Number of power socket outlets	20 IEC 60320 C13 4 IEC 60320 C19
--------------------------------	-------------------------------------

### Conformance

Product Certifications	cUL Listed METI Denan PSE UL Listed
Standards	CSA C22.2 No. 60950-1-03 UL 60950-1

### Environmental

Ambient Air Temperature for Operation	32...113 °F (0...45 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

### Ordering and shipping details

Category	11309-APC RESALE PRODUCTS
Discount Schedule	APC1
GTIN	731304225560
Nbr. of units in pkg.	1
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	No
Country of origin	IN

### Packing Units

Package 1 Height	83.50 in (212.1 cm)
Package 1 width	5.98 in (15.2 cm)
Package 1 Length	5.00 in (12.7 cm)
Number of Units in Package 3	42

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Lead free	Yes
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------