

Product data sheet

Specifications



Power Cord, Locking C19 to 5-20P, 3.0m

AP8751

Overview

| | |
|--------------|---|
| Presentation | Free up space and secure power cords between rack-mount PDUs and attached IT equipment with this exclusive easy-to-use cord retention method. While these cords will fit into any standard IEC receptacle or power inlet; the "locking" feature is enabled only when used with APC AP8000 series Rack PDUs or IT equipment with built-in locking receptacles. These locking connectors reduce the probability of accidentally disconnecting cords and dropping loads. |
| Lead time | Usually in Stock |

Main

| | |
|---------------------|------------|
| Main Output Voltage | 120 V |
| Plug standard | NEMA 5-20P |
| Cable length | 3.00 m |
| Number of cables | 1 |

Physical

| | |
|---------------------|--------------------|
| Colour | Black |
| Height | 23 cm |
| Width | 23 cm |
| Depth | 4.5 cm |
| Net weight | 0.71 kg |
| Mounting preference | No preference |
| Mounting mode | Not rack-mountable |

Input

| | |
|----------------------|------|
| Max line current | 20 A |
| Input current limits | 20 A |

Output

| | |
|--------------------------------|-----------------|
| Max current draw | 20 A |
| Number of power socket outlets | 1 IEC 60320 C19 |
| Power cable length | 3.05 m |

Conformance

| | |
|------------------------|-----|
| Product certifications | CSA |
|------------------------|-----|

Environmental

| | |
|---------------------------------------|-------------------|
| Ambient air temperature for operation | 0...105 °C |
| Relative humidity | 20...80 % |
| Operating altitude | 0...10000 ft |
| Ambient air temperature for storage | -25...105 °C |
| Storage Relative Humidity | 20...80 % |
| Storage altitude | 0.00...15240.00 m |

Packing Units

| | |
|------------------------------|----------------|
| Package 1 Weight | 0.71 kg |
| Package 1 Height | 23 cm |
| Package 1 width | 23 cm |
| Package 1 Length | 4.5 cm |
| SCC14 | 10731304279744 |
| Number of Units in Package 3 | 750 |

Offer Sustainability

| | |
|---------------------------|--|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Lead free | Yes |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | End of Life Information |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov |
| Take-back | Take-back program available |

Contractual warranty

| | |
|----------|---------------------------|
| Warranty | 2 years repair or replace |
|----------|---------------------------|