

Product data sheet

Specifications



Branch unit, EZ Meter-Pak, 225A, 3 sockets, 208Y/120VAC, lever bypass, ringless, 1200A Al/Cu busbar

EZML333225

Product availability : Stock - Normally stocked in distribution facility

Price* : 7,794.00 USD

Main

Product	Meter Center Branch Unit
Current Rating	225 A
Type	Meter-Pak
Bus Rating	1200 A
Number of Jaws	7 with jaw release
Number of Meter Sockets	3
Bypass Type	Lever bypass
Socket Type	Ringless

Complementary

Certifications	UL Listed
Busbar Material	Aluminium/copper busbar
Enclosure Material	Steel
Enclosure Rating	NEMA 3R
Maximum Voltage Rating	208Y/120 V AC 240/120 V delta AC
Mounting	Surface
Phase	3 phase in 3 phase out
Wire Configuration	4-wire
Height	53.06 in (1347.72 mm)
Width	19.44 in (493.78 mm)
Depth	9.44 in (239.78 mm)

Ordering and shipping details

Category	00020-EZ METER-PAK
Discount Schedule	DE4
GTIN	785901408819

* Price is “List Price” and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Returnability	Yes
Country of origin	MX
Packing Units	
Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.98 in (27.9 cm)
Package 1 Width	21.89 in (55.6 cm)
Package 1 Length	54.49 in (138.4 cm)
Package 1 Weight	170.00 lb(US) (77.111 kg)
Offer Sustainability	
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Contractual warranty	
Warranty	18 months
Recommended replacement(s)	