

# Product data sheet

Specifications



Branch unit, EZ Meter-Pak, 225A, 4 sockets, 208Y/120VAC, lever bypass, ringless, 1200A Al/Cu busbar

EZML334225

Product availability : Stock - Normally stocked in distribution facility

Price\* : 10,667.00 USD

## Main

Product	Meter Center Branch Unit
Current Rating	225 A
Type	Meter-Pak
Bus Rating	1200 A
Number of Jaws	7 with jaw release
Number of Meter Sockets	4
Bypass Type	Lever bypass
Socket Type	Ringless

## Complementary

Certifications	UL Listed
Busbar Material	Aluminium/copper busbar
Enclosure Material	Steel
Enclosure Rating	NEMA 3R
Maximum Voltage Rating	208Y/120 V AC 240/120 V delta AC
Mounting	Surface
Phase	3 phase in 3 phase out
Wire Configuration	4-wire
Height	67.06 in (1703.32 mm)
Width	19.44 in (493.78 mm)
Depth	9.44 in (239.78 mm)

## Ordering and shipping details

Category	00020-EZ METER-PAK
Discount Schedule	DE4
GTIN	785901299998

\* Price is “List Price” and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Returnability	Yes
Country of origin	MX
<b>Packing Units</b>	
Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.30 in (28.7 cm)
Package 1 Width	21.69 in (55.1 cm)
Package 1 Length	71.18 in (180.8 cm)
Package 1 Weight	209.00 lb(US) (94.801 kg)
<b>Offer Sustainability</b>	
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS declaration</a>
RoHS exemption information	<a href="#">Yes</a>
<b>Contractual warranty</b>	
Warranty	18 months
<b>Recommended replacement(s)</b>	