

ENCLOSURES

SAGINAW ENCLOSURE ACCESSORIES

LATCHES, LOCKS, VENTILATION, HEATING, COOLING



DESCRIPTION

Many **Saginaw** enclosure applications require keyed locks, venting, heating and/or cooling. These accessories will help to complete your panel projects.

ORDERING INFORMATION

MODEL	DESCRIPTION	ENCLOSURE
SCEDKLD	Cylinder lock, chrome	NEMA 1
SCENLTH	T-handle latch, non-locking	NEMA 1



SCEDKLD



SCENLTH

ORDERING INFORMATION

LOUVER KITS	DIMENSIONS in (cm)	CUT-OUT SIZE in (cm)
SCEAVK33	3.88 x 4.50 (9.9 x 11.4)	2.62 x 3.00 (6.7 x 7.6)
SCEAVK43	4.50 x 5.50 (11.4 x 14)	3.25 x 4.00 (8.3 x 10.2)
SCEAVK64	5.62 x 7.50 (14.2 x 19)	4.38 x 6.00 (11.1 x 15.2)
SCEAVK84	5.81 x 9.50 (14.8 x 24.1)	4.56 x 8.00 (11.6 x 20.3)

FILTERS	DIMENSIONS in (cm)	USED WITH
SCEFLT33	3.22 x 3.25 (8.2 x 8.3)	SCEAVK33
SCEFLT43	3.84 x 4.25 (9.8 x 10.8)	SCEAVK43
SCEFLT64	4.45 x 6.25 (11.3 x 15.9)	SCEAVK64
SCEFLT84	4.64 x 8.25 (11.8 x 21)	SCEAVK84



SCEAVK33



SCEFLT33

ORDERING INFORMATION

ELECTRIC HEATERS

ENCLOSURE SURFACE AREA (Sq Ft) = $2[(L \times W) + (L \times D) + (W \times D)]/144$

Mounting - 100/200 watt requires 1" clearance on sides and bottom and 4" above
Heater 4"W x 5"H x 6"D (10.16 cm x 12.7 cm x 114 cm)

400/800 watt requires 1" clearance on sides and bottom and 6" above
Heater 4"W x 7.5"H x 4.58"D (10 cm x 19 cm x 11.4 cm)

MODEL	WATTS	VOLTAGE (VAC)	Hz	AMPS	WEIGHT lb (kg)
SCEHF1251A	125	115	60	1.1	4 (1.8)
SCEHF2001A	200	115	60	1.7	4 (1.8)
SCEHF4001B	400	115	60	3.5	4 (1.8)
SCEHF8001B	800	115	60	7	4 (1.8)



SCEHF1251A



SCECF4



SCE112399

ORDERING INFORMATION

COOLING FANS (1 guard included, 2 recommended) 115 VAC 50/60 Hz

FAN #	CFM	SIZE in (cm)	SHAPE	GUARD #	BRACKET #
SCECF4	100	4.69 (11.92)	Square	SCEGARD4	SCE112399
SCECF6	240	6.72 (17.07)	Round	SCEGARD6	SCE111252
SCECF10	560	10.00 (25.4)	Round	SCEGARD10	SCE110551



SCE-GARD4

ORDERING INFORMATION PLUGGIT

MODEL	DIAMETER	FITS
HPSERIES1	0.50" - 0.56"	
HPSERIES1.5	0.88"	1/2" Conduit
HPSERIES2	0.88" - 1.00"	1/2" Conduit, 22mm PB
HPSERIES3	1.38" - 1.50"	1" Conduit, 1 1/4"
HPSERIES4	2.00" - 2.56"	1 1/2" Conduit, 2" Conduit



Pluggit



5

ENCLOSURES