



## Features

- UL Listed to meet code requirements
- 96VA load capacity
- Output On/Off control switch
- Breaker protected 24Vac Output
- Simple power connections
- Useful 120Vac convenience outlet
- Installation ready



## Catalog # LD02100 Enclosed Power Supply

The **UL Listed CPS120-024-100 Power Supply** is a sturdy self-contained power source rated @ 96VA. It provides simple power connections and has an illuminated control switch on the 24V output, which is fitted with a protective circuit breaker. The unit also provides a convenient unswitched 120V power point and is installation ready.



## Specifications

- Input:** 120VAC, 60Hz, 6 Amp max. (1Amp max. used by 24V supply).
- Output:** 24VAC, 60Hz, 4Amp max. continuous.  
120VAC, 60Hz, 5Amp max at convenience outlet. (Unswitched)
- Protective Device:** 24VAC supply with 4Amp re-settable thermal circuit breaker.  
120VAC supply, none.
- Controls:** Double pole switch with power indicating lamp, fitted on the primary of the 24V transformer. 120V convenience outlet power uncontrolled.
- Connections:** One 5 position terminal block with combination head screws and wire clamps. Provided connection for 120VAC input, 24VAC output and safety ground.
- Enclosure:** Three piece steel enclosure, with 4, 1/4" O mounting holes, and standard 7/8" Ø, top and bottom knockouts. Removable outer cover fitted with an indicator lamp 'peephole', and a removable control switch access plate.
- Dimensions:** 6 1/8" H x 5 1/4" W x 4 1/4" D.
- Operating Temp:** -15°F to 140°F (-25°C to 60°C).
- Weight:** 6.10 Lbs. (2.8 Kg.)
- Standard Accessories:** Instruction/ Installation sheet, Warranty Card.
- Safety Approvals:** UL Listed for the US and Canada, UL File # E207801

## Ordering Information

Catalog #	Mfg #	Description
LD02100	CPS120-024-100	Enclosed 96VA Power Supply