



ENCLOSURES

HOFFMAN ENCLOSURE ACCESSORIES

LOCKS, LATCHES, VENTILATION, HEATING, COOLING

ORDERING INFORMATION

MODEL	DESCRIPTION	ENCLOSURE
A-L12AR	Cylinder lock	NEMA 1
A-L7A	T-handle latch	NEMA 1
A-L2A	One-point latch kit	NEMA 12
A-L2BR	Three-point latch kit for 16", 20", 24", or 30"H enclosures	NEMA 12
A-L2CR	Three-point latch kit for 36", 42", or 48"H enclosures	NEMA 12
A-L2DR	Three-point latch kit for 60" or 72"H enclosures	NEMA 12



A-L12AR



A-L2A



A-L7A



ORDERING INFORMATION

LOUVER KITS	DIMENSIONS in (cm)	CUT-OUT SIZE in (cm)
A-VK33	3.88 x 4.50 (9.9 x 11.4)	2.62 x 3.00 (6.7 x 7.6)
A-VK43	4.50 x 5.50 (11.4 x 14)	3.25 x 4.00 (8.3 x 10.2)
A-VK64	5.62 x 7.50 (14.2 x 19)	4.38 x 6.00 (11.1 x 15.2)
A-VK84	5.81 x 9.50 (14.8 x 24.1)	4.56 x 8.00 (11.6 x 20.3)

FILTERS	DIMENSIONS in (cm)	USED WITH
A-FLT33	3.22 x 3.25 (8.2 x 8.3)	A-VK33
A-FLT43	3.84 x 4.25 (9.8 x 10.8)	A-VK43
A-FLT64	4.45 x 6.25 (11.3 x 15.9)	A-VK64
A-FLT84	4.64 x 8.25 (11.8 x 21)	A-VK84

DECORATIVE VENT KIT (includes filter)	DIMENSIONS in (cm)
X-PV32	11.81 x 7.88 x 1.03 (30 x 20 x 2.6)



Louver Plate Kit
A-VK33



Filters for
Louver Plate Kit
A-FLT33



Decorative
Vent Kit
X-PV32

ORDERING INFORMATION

ELECTRIC HEATERS

ENCLOSURE SURFACE AREA (Sq Ft) = 2[(LxW) + (LxD) + (WxD)]/144

Mounting - 100/200 watt requires 1" clearance on sides and bottom and 4" above
Heater 4"W x 5"H x 4"D (10.16 cm x 12.7 cm x 10.2 cm)

400/800 watt requires 1" clearance on sides and bottom and 6" above
Heater 4.25"W x 7"H x 4.38"D (10.8 cm x 17.8 cm x 11.1 cm)

MODEL	WATTS	VOLTAGE (VAC)	Hz	AMPS	WEIGHT lb (kg)	Desired ambient temperature rise °F					
						10°F	20°F	30°F	40°F	50°F	60°F
D-AH1001A	100	120	50/60	0.9	4 (1.8)	30	15	10	5	—	—
D-AH2001A	200	120	50/60	1.7	4 (1.8)	50	25	15	14	12	8
D-AH4001B	400	120	50/60	3.3	6 (2.7)	—	50	30	23	19	16
D-AH8001B	800	120	50/60	6.5	6 (2.7)	—	—	—	50	35	28



Electric Heater



Cooling Fans
A-4AXFN



Fan Bracket
A-BRKT4

ORDERING INFORMATION

COOLING FANS (1 guard included, 2 recommended) 115 VAC 50/60 Hz

FAN #	CFM	SIZE in (cm)	SHAPE	GUARD #	BRACKET #
A-4AXFN	100	4.69 (11.92)	Square	A-GARD4	A-BRKT4
A-6AXFN	240	6.72 (17.07)	Round	A-GARD6	A-BRKT6
A-10AXFN	560	10.00 (25.4)	Round	A-GARD10	A-BRKT10



Additional
Fan Guard
A-GARD4



SAGINAW ENCLOSURE ACCESSORIES LATCHES, LOCKS, VENTILATION, HEATING, COOLING

DESCRIPTION

Many enclosure applications require keyed locks, venting, heating and/or cooling. These accessories will help to complete your panel projects.



ORDERING INFORMATION

MODEL	DESCRIPTION	ENCLOSURE
SCEDKLD	Cylinder lock, chrome	NEMA 1
SCENLTH	T-handle latch, non-locking	NEMA 1



SCEDLKLD



SCENLTH



ORDERING INFORMATION

LOUVER KITS	DIMENSIONS in (cm)	CUT-OUT SIZE in (cm)
SCEAVK33	3.88 x 4.50 (9.9 x 11.4)	2.62 x 3.00 (6.7 x 7.6)
SCEAVK43	4.50 x 5.50 (11.4 x 14)	3.25 x 4.00 (8.3 x 10.2)
SCEAVK64	5.62 x 7.50 (14.2 x 19)	4.38 x 6.00 (11.1 x 15.2)
SCEAVK84	5.81 x 9.50 (14.8 x 24.1)	4.56 x 8.00 (11.6 x 20.3)
FILTERS	DIMENSIONS in (cm)	USED WITH
SCEFLT33	3.22 x 3.25 (8.2 x 8.3)	SCEAVK33
SCEFLT43	3.84 x 4.25 (9.8 x 10.8)	SCEAVK43
SCEFLT64	4.45 x 6.25 (11.3 x 15.9)	SCEAVK64
SCEFLT84	4.64 x 8.25 (11.8 x 21)	SCEAVK84



SCEAVK33



SCEFLT33

ORDERING INFORMATION

ELECTRIC HEATERS

ENCLOSURE SURFACE AREA (Sq Ft) = 2[(LxW) + (LxD) + (WxD)]/144

Mounting - 100/200 watt requires 1" clearance on sides and bottom and 4" above
Heater 4"W x 5"H x 4"D (10.16 cm x 12.7 cm x 11.4 cm)
400/800 watt requires 1" clearance on sides and bottom and 6" above
Heater 4"W x 7.5"H x 4.58"D (10 cm x 19 cm x 11.4 cm)

MODEL	WATTS	VOLTAGE (VAC)	Hz	AMPS	WEIGHT lb (kg)
SCEHF1251A	125	115	60	1.1	4 (1.8)
SCEHF2001A	200	115	60	1.7	4 (1.8)
SCEHF4001B	400	115	60	3.5	4 (1.8)
SCEHF8001B	800	115	60	7	4 (1.8)



SCEHF1251A

ORDERING INFORMATION


COOLING FANS (1 guard included, 2 recommended) 115 VAC 50/60 Hz					
FAN #	CFM	SIZE in (cm)	SHAPE	GUARD #	BRACKET #
SCECF4	100	4.69 (11.92)	Square	SCEGARD4	SCE112399
SCECF6	240	6.72 (17.07)	Round	SCEGARD6	SCE111252
SCECF10	560	10.00 (25.4)	Round	SCEGARD10	SCE110551



SCECF4



SCE112399



SCE-GARD4