


Product data sheet

Specifications



Electric motor MCH, MasterPact MTZ2/MTZ3, remote operation, 100/130VDC, spare part

LV847890SP

Main

Range	Masterpact
Device short name	MCH
Product or component type	Motor mechanism
Device application	Control
Range compatibility	Masterpact (MasterPact MTZ2) Masterpact (MasterPact MTZ3)

Complementary

Control type	Standard
[Uc] control circuit voltage	100...130 V DC
Threshold tripping voltage	0.85...1.1 Un
Maximum power consumption in VA	180 VA
Overcurrent protection	2...3 x In 0.1 s
Maximum charging time	4 s
Maximum operating frequency	<= 3 cycles per minute
Provided contact	Limit switch contact at 240 V 10 A

Environment

Provided equipment	1 instruction sheet
Offer type	Spare part

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	12.7 cm
Package 1 Width	13.1 cm
Package 1 Length	22.9 cm
Package 1 Weight	1.921 kg
Unit Type of Package 2	S03
Number of Units in Package 2	6

Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	11.969 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov