

# Product data sheet

Specifications

SQUARE D

Green Premium™



Panelboard interior, NQ, main lugs, 225A, Cu bus, 30 pole spaces, 1 phase, 3 wire, 240VAC, 48VDC

NQ30L2C

Product availability : Stock - Normally stocked in distribution facility

Price\* : 1,179.00 USD

## Main

Panelboard Type	Main lugs
Product or Component Type	Interiors
Branch Circuit Breaker Type	QOB QOB-VH QHB
Busbar Material	Copper

## Complementary

Number of spaces	30
Enclosure Nominal Height	32 in (812.80 mm)
Enclosure Nominal Width	20 in (508.00 mm)
Enclosure Nominal Depth	5.75 in (146.05 mm) NEMA 1 6.5 in (165.10 mm) NEMA 3R/5/12
Line Rated Current	225 A
[lu] rated interrupted current	10 kA 22 kA 65 kA
Wiring configuration	3-wire
Number of Phases	1 phase
Voltage Rating	240 V AC 48 V DC
Tightening torque	40.01...50.01 lbf.in (4.52...5.65 N.m) 0.02...0.10 in² (13.30...67.43 mm²) (AWG 6...AWG 2/0) 100.01 lbf.in (11.3 N.m) 0.02...0.10 in² (13.30...67.43 mm²) (AWG 6...AWG 2/0) 274.99 lbf.in (31.07 N.m) 0.02...0.27 in² (13.30...177.3 mm²) (AWG 6...350 kcmil) 274.99 lbf.in (31.07 N.m) 0.02...0.20 in² (13.30...126.7 mm²) (AWG 6...250 kcmil) 274.99 lbf.in (31.07 N.m) 0.17...0.24 in² (107.2...152 mm²) (AWG 4...300 kcmil)
Height	27 in (685.80 mm)
Width	10.44 in (265.18 mm)

## Environment

Standards	UL CSA
-----------	-----------

## Ordering and shipping details

Category	09151-NQ RTA PANELBOARDS
----------	--------------------------

\* Price is “List Price” and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Discount Schedule	PE1A
GTIN	785901502029
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.50 in (16.51 cm)
Package 1 Width	14.00 in (35.56 cm)
Package 1 Length	32.00 in (81.28 cm)
Package 1 Weight	16.50 lb(US) (7.484 kg)
Unit Type of Package 2	PAL
Number of Units in Package 2	18
Package 2 Height	40.00 in (101.6 cm)
Package 2 Width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)
Package 2 Weight	336.00 lb(US) (152.407 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)