

Product data sheet

Specifications



Terminal Blocks, Linergy, plugin bridge jumper, for 6.2mm wide blocks, 3 points, red

NSYTRAL43

Product availability : Stock - Normally stocked in distribution facility

Price* : 1.50 USD

Main

Range	Linergy
Product name	Linergy TR
Product or Component Type	Plug-in bridge
Device short name	TRA
Accessory / separate part category	Connection accessory
Product compatibility	TRV screw terminal terminal block TRP push-in terminal block TRR spring terminal terminal block TRH IDC terminal block
Number of ways	3 ways

Complementary

Cable cross section	0.01 in² (4 mm²)
Number of connections	4 2 3
Number of measurement input	2 1 3 6 4
Quantity per Set	Set of 50
Net Weight	0.11 oz (3 g)
Color	Red

Ordering and shipping details

Category	21715-IEC TERMINAL BLOCKS-NSY,AM1,DF6,GK1
Discount Schedule	CP5
GTIN	3606480534140
Returnability	Yes
Country of origin	DE

* Price is “List Price” and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.59 in (1.5 cm)
Package 1 Width	4.72 in (12.0 cm)
Package 1 Length	6.30 in (16.0 cm)
Package 1 Weight	0.07 oz (2.0 g)
Unit Type of Package 2	S01
Number of Units in Package 2	250
Package 2 Height	5.91 in (15.0 cm)
Package 2 Width	5.91 in (15.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	32.31 oz (916.0 g)
Unit Type of Package 3	BAG
Number of Units in Package 3	50
Package 3 Height	0.59 in (1.5 cm)
Package 3 Width	4.72 in (12.0 cm)
Package 3 Length	6.30 in (16.0 cm)
Package 3 Weight	5.22 oz (148.0 g)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Halogen content performance	Halogen free plastic parts product

Contractual warranty

Warranty	18 months
----------	-----------