

POWER SUPPLIES



FUNCTIONAL DEVICES ENCLOSED 24 VAC CLASS 2 POWER SOURCE

PSB40AB10, PSB100AB10, PSC40AB10, PSC100AB10

Functional Devices, Inc.



POWER SUPPLIES

16

DESCRIPTION

The **Functional Devices PSC40AB10** and **PSC100AB10** are 24VAC Class 2 power sources pre-packaged in a metal enclosure. The panel-mount versions, **PSB40AB10** and **PSB100AB10**, are provided without the metal enclosure. These units are available with either 40VA or 100VA power ratings. All models accept 120VAC input and are provided with a combination on/off switch/circuit breaker to control the output and a combination on/off switch/breaker to control the incoming 120VAC power. Other handy features include a 120VAC convenience outlet, LED indication of the output and terminal strip wiring.

FEATURES

- Enclosed or panel mount models
- Combination on/off switch/circuit breakers for the input and output
- Convenience outlet
- Terminal strip wiring
- LED indication of the output
- Class 2 UL Listed



**PSB40AB10
(Panel Mount)**



**PSC40AB10
(Cover Removed)**




**PSC40AB10
(Covered, Wall Mount)**

SPECIFICATIONS

Supply Voltage	120 VAC, 50/60 Hz	Output Indication	Red LED for 24 VAC output
Output Voltage	24 VAC	Over Current Protection	
Input Control	Combination on/off switch and 10A circuit breaker. Controls input power to entire unit.	PSC100AB10	4A circuit breaker
Convenience Outlet	120 VAC, 9A	PSC40AB10	3A circuit breaker
Secondary Voltage	24 VAC, Class 2	Enclosure Rating	NEMA1, with outlet and breaker access cover
Output Control		Weight	
PSX100AB10	Combination on/off switch and 4A circuit breaker. Controls 24 VAC output only.	PSC40	5.31 lb (2.41 Kg)
PSX40AB10	Combination on/off switch and 3A circuit breaker. Controls 24 VAC output only.	PSC100	6.70 lb (3.04 Kg)
		PSB40	3.21 lb (1.5 Kg)
		PSB100	4.51 lb (2.05 Kg)
		Approvals	UL Class 2, UL916, File E190394, CE, RoHS
		Warranty	1 year

WIRING



ORDERING INFORMATION

MODEL	DESCRIPTION
PSB40AB10	120 VAC to 24 VAC, 40 VA, with 10A main & 3A secondary breaker, panel mount
PSB100AB10	120 VAC to 24 VAC, 100 VA, with 10A main & 4A secondary breaker, panel mount
PSC40AB10	120 VAC to 24 VAC, 40 VA enclosed, with 10A main & 3A secondary breaker
PSC100AB10	120 VAC to 24 VAC, 100 VA enclosed with 10A main & 4A secondary breaker

* -IC indicates UL508 and -TC indicates terminal cover