



ENCLOSURES

SAGINAW SUBPANELS AND PERF PANELS FOR SCE ENCLOSURES SCE SUBPANELS AND PERF PANELS

DESCRIPTION

The Saginaw SCExPx subpanels are flat subpanels and powder coated in white. The Saginaw SCExNxMPP perforated subpanels have 0.13" mounting holes with 0.25" staggered patterns for the installation of lightweight control components with #8 self threading screws, for use in small and medium size Type 1 enclosures. The perforated subpanels are also powder coated in white.

NEW!



5

FEATURES

- Flat, powder coated white*
- Perforated subpanels with mounting holes*
- Variety of sizes and custom sizes available*

ORDERING INFORMATION

MODEL	DIMENSIONS Size (in) H x W	MODEL	DIMENSIONS Size (in) H x W	MODEL	DIMENSIONS Size (in) H x W
SCE6P4	4.88" x 2.88"	SCE24P20	21" x 17"	SCE64P25	60" x 21.75"
SCE6P6	4.88" x 4.88"	SCE24P24	21" x 21"	SCE64P31	60" x 27.75"
SCE8P6	6.75" x 4.88"	SCE24N20MP	22" x 18"	SCE64P37	60" x 33.75"
SCE8P8	6.75" x 6.88"	SCE24N16MP	24" x 16"	SCE64P52	60" x 48"
SCE6N6MP	6" x 6"	SCE24N24MP	24" x 24"	SCE64P64	60" x 60"
SCE8N6MP	8" x 6"	SCE30P16	27" x 13"	SCE64P76	60" x 72"
SCE8N8MP	8" x 8"	SCE30P24	27" x 21"	SCE72P60	68" x 56"
SCE10P8	8.75" x 6.88"	SCE30P30	27" x 27"	SCE72P72	68" x 68"
SCE10P10	8.75" x 8.88"	SCE30P20	27" x 17"	SCE72P30	69" x 27"
SCE12P24	9" x 21"	SCE30N24MP	30" x 24"	SCE72P36	69" x 33"
SCE12DLP12	9" x 9"	SCE30N30MP	30" x 30"	SCE76P37	72" x 33.75"
SCE10N10MP	10" x 10"	SCE36P16	33" x 13"	SCE76P76	72" x 72"
SCE10N8MP	10" x 8"	SCE36P24	33" x 21"	SCE82P37	78" x 33.75"
SCE12P12	10.75" x 10.88"	SCE36P30	33" x 27"	SCE82P76	78" x 72"
SCE12P6	10.75" x 4.88"	SCE36P36	33" x 33"	SCE12N12MPP	Perforated 10" x 10"
SCE12P10	10.75" x 8.88"	SCE36N24MP	36" x 24"	SCE12N10MPP	Perforated 10" x 8"
SCE12N10MP	12" x 10"	SCE36N30MP	36" x 30"	SCE14N12MPP	Perforated 12" x 10"
SCE12N12MP	12" x 12"	SCE40P24	37" x 21"	SCE16N12MPP	Perforated 14" x 10"
SCE14P12	12.75" x 20.88"	SCE42P24	39" x 21"	SCE16N16MPP	Perforated 14" x 14"
SCE14P8	12.75" x 6.88"	SCE42P30	39" x 27"	SCE20N16MPP	Perforated 18" x 14"
SCE16DLP14	13" x 11"	SCE42P36	39" x 33"	SCE20N20MPP	Perforated 18" x 18"
SCE16P16	13" x 13"	SCE42P42	39" x 39"	SCE24N16MPP	Perforated 22" x 14"
SCE16P12	13" x 9"	SCE48P24	45" x 21"	SCE24N20MPP	Perforated 22" x 18"
SCE14N12MP	14" x 12"	SCE48P30	45" x 27"	SCE24N24MPP	Perforated 22" x 22"
SCE16P14	14.75" x 12.88"	SCE48P36	45" x 33"	SCE30N24MPP	Perforated 28" x 22"
SCE16P10	14.75" x 8.88"	SCE48P42	45" x 39"	SCE30N30MPP	Perforated 28" x 28"
SCE16N12MP	16" x 12"	SCE48P48	45" x 45"	SCE36N24MPP	Perforated 34" x 22"
SCE16N16MP	16" x 16"	SCE60PC36	55.63" x 33"	SCE36N30MPP	Perforated 34" x 28"
SCE20P16	17" x 13"	SCE60BFP42	56" x 38"	SCE6N6MPP	Perforated 4" x 4"
SCE20P20	17" x 17"	SCE60P48	56" x 44"	SCE8N6MPP	Perforated 6" x 4"
SCE20P12	17" x 9"	SCE60P60	56" x 56"	SCE8N8MPP	Perforated 6" x 6"
SCE20N16MP	20" x 10"	SCE60P24	57" x 21"	SCE10N8MPP	Perforated 8" x 6"
SCE20N20MP	20" x 20"	SCE60P30	57" x 27"	SCE10N10MPP	Perforated 8" x 8"
SCE24P16	21" x 13"	SCE60P36	57" x 33"	SCE36P30AL	33" x 27" Aluminum