

# SEBOX

## Universal Enclosure Series



### Product Description

The SEBOX is a UL NEMA 4 rated enclosure that allows for both indoor and outdoor applications. All enclosures come with a gland plate for easy wiring access.

### Features

- Large embedded cable-entry plate with neoprene seal
- Standard 3-mm double-bar lock with screw driver lock feature
- Rated NEMA 4
- Outdoor installation compliant with IEC 62208
- Foamed-in polyurethane gasket doors that guarantee water and dust tightness
- Easily removable and reversible door with invisible metal hinges allowing the door to open 120°
- Available with optional field-installed perforated subpanel
- UL Listed, file # E189035
- Epoxy-polyester resin finish, color RAL 7035 grey
- Included Schneider Electric logo label allows left- and right-hand door options. Enclosure comes standard left-hand.

### Available Products

Item	Description	Dimensions HxWxD in. (mm)	Perf. Panel Dimensions HxW in. (mm)	Weight lbs. (kg)
SEBOX121806	12x18x6 enclosure	11.8 (300) x 17.7 (450) x 5.9 (150)		16.7 (6.5)
SEBOX121806P	12x18x6 enclosure with perforated panel	11.8 (300) x 17.7 (450) x 5.9 (150)	9.5 (241.3) x 15.5 (393.7)	18.6 (8.4)
SEBOX161608	16x16x8 enclosure	15.6 (400) x 15.6 (400) x 7.9 (200)		17.6 (8.0)
SEBOX161608P	16x16x8 enclosure with perforated panel	15.6 (400) x 15.6 (400) x 7.9 (200)	13.6 (345.4) x 13.6 (345.4)	20.1 (9.1)
SEBOX202010	20x20x10 enclosure	19.7 (500) x 19.7 (500) x 9.8 (250)		28.2 (12.8)
SEBOX202010P	20x20x10 enclosure with perforated panel	19.7 (500) x 19.7 (500) x 9.8 (250)	17.5 (444.5) x 17.5 (444.5)	32.3 (14.7)
SEBOX242410	24x24x10 enclosure	23.6 (600) x 23.6 (600) x 9.8 (250)		33.28 (15.1)
SEBOX242410P	24x24x10 enclosure with perforated panel	23.6 (600) x 23.6 (600) x 9.8 (250)	21.7 (551.2) x 21.7 (551.2)	39.48 (17.9)
SEBOX322410	32x24x10 enclosure	31.5 (800) x 23.62 (600) x 9.84 (250)		44.0 (20.0)
SEBOX322410P	32x24x10 enclosure with perforated panel	31.5 (800) x 23.62 (600) x 9.84 (250)	29.25 (743) x 21.5 (546)	53.0 (24.0)
SEBOX392410	39x24x10 enclosure	39.4 (1000) x 23.6 (600) x 9.8 (250)		62.8 (28.4)
SEBOX392410P	39x24x10 enclosure with perforated panel	39.4 (1000) x 23.6 (600) x 9.8 (250)	37.5 (952.5) x 21.7 (551.2)	71.7 (32.5)
SEBOX393210	39x32x10 enclosure	39.4 (1000) x 31.5 (800) x 9.8 (250)		76.0 (34.5)
SEBOX393210P	39x32x10 enclosure with perforated panel	39.4 (1000) x 31.5 (800) x 9.8 (250)	37.5 (952.5) x 29.5 (749.3)	87.33 (39.6)
SEBOX483212	48x32x12 enclosure	47.2 (1200) x 31.5 (800) x 11.8 (300)		99.2 (45.0)
SEBOX483212P	48x32x12 enclosure with perforated panel	47.2 (1200) x 31.5 (800) x 11.8 (300)	45 (1143) x 29.3 (744.2)	115.8 (52.5)

USA: +1 888-444-1311  
 Europe: +46 10 478 2000  
 Asia: +65 6484 7877  
[www.schneider-electric.com](http://www.schneider-electric.com)

**Schneider**  
 Electric