

Product data sheet

Characteristics

8911DPSG23V09

8911DPS definite purpose starter, 25 A, 3P,
208/240 V 60 Hz / 220 V 50 Hz coil, NEMA 1

Product availability : Stock - Normally stocked in distribution facility



Price** : 412.02 USD



Main

Product	Definite Purpose Starter
Ampere Rating	25 A
Horsepower Rating	2 hp 115 V AC, 1 phase 5 hp 230 V AC, 1 phase 10 hp 230 V AC, 3 phase 15 hp 460 V AC, 3 phase 20 hp 575 V AC, 3 phase
Maximum Voltage Rating	600 V AC
Control Circuit Voltage	220 V AC 50 Hz 208...240 V AC 60 Hz
Phase	3 phase

Complementary

Enclosure Material	Painted sheet steel
Enclosure Rating	NEMA 1
Locked Rotor Amperes	150 A 230 V AC 125 A 460 V AC 100 A 575 V AC
Number of Poles	3P
Range	DPS
Overload Type	Melting alloy
Number of Thermal Units	3

Ordering and shipping details

Category	21381 - 8911 DP
Discount Schedule	CP1
GTIN	00785901024682
Package weight(Lbs)	2.66 kg (5.87 lb(US))

Jan 8, 2020

Returnability	Yes
Country of origin	CN

Offer Sustainability

EU RoHS Directive	Not compliant
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.

Contractual warranty

Warranty	18 months
----------	-----------