

Product availability : Stock - Normally stocked in distribution facility



Price* : 496.44 USD



Main

Product	Definite Purpose Starter
Line Rated Current	40 A
Horsepower Rating	3 hp 115 V AC 1 phase 10 hp 230 V AC 3 phases 7.5 hp 230 V AC 1 phase 20 hp 460 V AC 3 phases 25 hp 575 V AC 3 phases
System Voltage	600 V AC
Control Circuit Voltage	220 V AC 50 Hz 208...240 V AC 60 Hz
Phase	3 phases

Complementary

Enclosure Material	Painted sheet steel
Enclosure Rating	NEMA 1
Locked Rotor Amperes	240 A 230 V AC 200 A 460 V AC 160 A 575 V AC
Number of Poles	3P
Range	DPS
Overload Type	Melting alloy
Number of Thermal Units	3

Ordering and shipping details

Category	21381 - 8911 DP
Discount Schedule	CP1
GTIN	00785901024712
Nbr. of units in pkg.	1
Package weight(Lbs)	5.6500000000000004

Returnability	Y
Country of origin	CN

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
California proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------