

# 9001BW245

## CONTROL STATION 600VAC 5A T-B Ø30

### Standard Duty Momentary Pushbuttons 1NO-1NC

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\*\* : 270.00 USD



#### Main

Range of product	Harmony 9001BW
Product or component type	Complete control station
Device short name	9001BW
Control station application	Two functions
Colour of base of enclosure	Grey

#### Complementary

Material	Cast aluminium
Cable entry	1 entry for 1/2" - 14 NPT
CAD overall width	2.76 in (70 mm)
CAD overall height	4.25 in (108 mm)
CAD overall depth	3.58 in (91 mm)
Type of operator	momentary
Control station composition	1 flush push-button, black, white ON 1 flush push-button, red, white OFF
Contacts type and composition	1 NO + 1 NC
Mechanical durability	5000000 cycles
[Ie] rated operational current	0.6 A 600 V, AC-1/DC-1 0.75 A 480 V, AC 1.5 A 240 V, AC 3.75 A 120 V, AC
Device mounting	Surface
Type of installation	Indoor/outdoor

#### Environment

Ambient air temperature for storage	-40...158 °F (-40...70 °C)
Ambient air temperature for operation	-13...158 °F (-25...70 °C)

NEMA degree of protection	NEMA 1 NEMA 4
Standards	JIS C 4520 EN/IEC 60947-1 EN/IEC 60947-5-4 EN/IEC 60947-5-1 EN/IEC 60947-5-5 UL 508 CSA C22.2 No 14
Product certifications	UL listed CSA
Environmental characteristic	Waterproof Dustproof

## Ordering and shipping details

Category	21421 - 9001 B (NOT BW70 - BW80)
Discount Schedule	CS1
GTIN	00785901857693
Returnability	No
Country of origin	MX

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds and Diisodecyl phthalate (DIDP) which is known to the State of California to cause Carcinogen and Reproductive harm. For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>

## Contractual warranty

Warranty	18 months
----------	-----------