



## Main

|                                 |                       |
|---------------------------------|-----------------------|
| Range of product                | Harmony 9001K         |
| Product or component type       | Push-button           |
| Device short name               | K                     |
| Operator additional information | Full guard in plastic |

## Complementary

|                                |                            |
|--------------------------------|----------------------------|
| Bezel material                 | Chromium plated metal      |
| Mounting diameter              | 30 mm                      |
| Light source                   | Without                    |
| Light block supply             | Without supply             |
| Contacts type and composition  | 2 NO + 2 NC                |
| [Ie] rated operational current | 10 A, AC-15<br>10 A, DC-13 |
| Contact operation              | Standard                   |
| Device presentation            | Complete product           |

## Environment

|                           |                                                                            |
|---------------------------|----------------------------------------------------------------------------|
| Product certifications    | NEMA<br>UL listed file E42259 CCN NKCR<br>CE<br>CSA LR 25490 class 3211 03 |
| NEMA degree of protection | NEMA 1/2/3/3R/4/6/12/13                                                    |

## Offer Sustainability

|                          |                                                                                                   |
|--------------------------|---------------------------------------------------------------------------------------------------|
| Sustainable offer status | Green Premium product                                                                             |
| REACH Regulation         | <a href="#">REACH Declaration</a>                                                                 |
| EU RoHS Directive        | Pro-active compliance (Product out of EU RoHS legal scope)<br><a href="#">EU RoHS Declaration</a> |
| Mercury free             | Yes                                                                                               |

|                            |                                                                                                                             |
|----------------------------|-----------------------------------------------------------------------------------------------------------------------------|
| RoHS exemption information | <a href="#">Yes</a>                                                                                                         |
| China RoHS Regulation      | <a href="#">China RoHS declaration</a>                                                                                      |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>                                                                               |
| Circularity Profile        | No need of specific recycling operations                                                                                    |
| WEEE                       | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |