Product data sheet Characteristics

9001KS34BH13 SELECTOR SWITCH 600VAC 10A 30MM T-K



Wall		
Range of product	Harmony 9001K	
Product or component type	Selector switch	
Device short name	К	9
Type of operator	Spring return (right to left)	
Operator profile	Black standard knob	

Complementary

Bezel material	Chromium plated metal	
Mounting diameter	30 mm	
Operator position information	2 positions	,
Contacts type and composition	1 C/O	
Connections - terminals	Screw-clamp terminals 1 x 0.222 x 1.5 mm² IEC 60947-1	
Product compatibility	9001KA1, mounting on side 2	
Device presentation	Complete product	

Environment

NEMA degree of protection	NEMA 1/2/3/3R/4/6/12/13
Product certifications	CE UL listed file E42259 CCN NKCR CSA LR24590 class 3211 03

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0921 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity	ф 20 20 20 20 20 20 20 20 20 20 20 20 20
REACh	Reference not containing SVHC above the threshold	. <u>.</u>
	Reference not containing SVHC above the threshold	<u>v</u> .