Product data sheet Characteristics

9001KS43BH1 SELECTOR SWITCH 600VAC 10A 30MM T-K



Main

- ITAIT		
Range of product	Harmony 9001K	e. H
Product or component type	Selector switch	, z
Device short name	К	
Type of operator	Maintained	
Operator profile	Black standard knob	÷
		7

Complementary

Bezel material	Chromium plated metal	
Mounting diameter	30 mm	
Operator position information	3 positions	
Connections - terminals	Screw-clamp terminals 1 x 0.222 x 1.5 mm² IEC 60947-1	
Device presentation	Complete product	

Environment

NEMA degree of protection	NEMA 1/2/3/3R/4/6/12/13	
Product certifications	UL listed file E42259 CCN NKCR CE CSA LR24590 class 3211 03	to for

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0921 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity	
REACh	Reference not containing SVHC above the threshold	— <u>:</u>
	Reference not containing SVHC above the threshold	: