

Product data sheet

Characteristics

9050JCK26V20

Plug In Timer, off delay, 0.1 to 10 minutes, 10 A at 240 VAC, 120 VAC/110 VDC

Product availability : Stock - Normally stocked in distribution facility



Price** : 107.00 USD



Main

Product range	9050JCK
Product type	Timer
Timing mode	Off-delay
Timing range	0.1...10 min
Supply voltage	120 V AC 110 V DC

Complementary

Power consumption	2 VA
Current rating	10 A
Switch function	DPDT
Contact composition	2 NO + 2 NC
Contact material	Silver nickel
Maximum switching voltage	240 V AC
Mounting type	Socket
Number of pins	11
Shape of pins	Tubular
For use with	8501NR61 8501NR62

Environment

Certifications	RoHS UL Recognized CE UL Listed
Ambient temperature range - operational	-18...150 °F (-28...66 °C)

Height	2.40 in (61 mm)
Width	1.69 in (43 mm)
Depth	4.09 in (104 mm)

Ordering and shipping details

Category	21651 - 9050 JCK(NOT JCK60, 70) G P TIMERS
Discount Schedule	CP2
GTIN	00785901032663
Returnability	Yes
Country of origin	US

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information

Contractual warranty

Warranty	18 months
----------	-----------