



Main

Range of product	Modicon M340 automation platform
Product or component type	Ethernet TCP/IP network module
Concept	Transparent Ready
Integrated connection type	Ethernet TCP/IP RJ45 10/100 Mbit/s 1 twisted pair transparent ready class B30
Protective treatment	TC

Complementary

Communication service	Web server configurable Modbus TCP messaging I/O scanning Global Data SNMP network administrator Rack Viewer FDR server Data Editor (via PC terminal) Bandwidth management
Port Ethernet	10BASE-T/100BASE-TX
Memory description	Supplied Flash memory card (BMXRWSC016M)
Memory usage	Activating the standard web server Application saving
Supply	Internal power supply via rack
Local signalling	1 LED red processor or system fault (ERR) 1 LED red memory card fault (CARD ERR) 1 LED red data rate (ETH 100) 1 LED green status of Ethernet network (ETH STS) 1 LED green processor running (RUN) 1 LED green activity on Ethernet network (ETH ACT)
Control type	RESET pushbutton cold restart
Current consumption	90 mA at 24 V DC
Module format	Standard
Product weight	0.2 kg

Environment

Ambient air temperature for operation	0...60 °C
Relative humidity	10...95 % without condensation
IP degree of protection	IP20
Marking	CE
Product certifications	UL 508
Standards	CSA C22.2 No 142 EN/IEC 61131-2 CSA C22.2 No 213 Class I Division 2

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS	Compliant - since 0722 - Schneider Electric declaration of conformity
REACH	Reference contains SVHC above the threshold - go to CaP for more details
Product environmental profile	Available Download Product Environmental
Product end of life instructions	Need no specific recycling operations

Modules Mounted on Racks

Dimensions



- (1) With removable terminal block (cage, screw or spring).
- (2) With FCN connector.
- (3) On AM1 ED rail: 35 mm wide, 15 mm deep. Only possible with BMXXBP0400/0400H/0600/0600H/0800/0800H rack.

Rack references	a in mm	a in in.
BMXXBP0400 and BMXXBP0400H	242.4	09.54
BMXXBP0600 and BMXXBP0600H	307.6	12.11
BMXXBP0800 and BMXXBP0800H	372.8	14.68
BMXXBP1200 and BMXXBP1200H	503.2	19.81