

Product availability : Stock - Normally stocked in distribution facility



Price** : 326.00 USD



Main

Product	Single Throw Safety Switch
Current Rating	60 A
Certifications	UL listed file E2875
Enclosure Rating	NEMA 1
Disconnect Type	Fusible disconnect switch
Factory Installed Neutral	Neutral (factory installed)
Short Circuit Current Rating	100 kA maximum depending on fuse H, K or R
Mounting Type	Surface
Number of Poles	3
Electrical Connection	Lugs
Duty Rating	General duty
Voltage Rating	240 V AC
Wire Size	AWG 12...AWG 3 aluminium AWG 14...AWG 3 copper

Complementary

Width	189.23 mm (7.45 in)
Height	377.95 mm (14.88 in)
Depth	123.70 mm (4.87 in)
Tightening torque	3.95 N.m (35 lbf.in) AWG 14...AWG 10) 3.95 N.m (35 lbf.in) 0.00...0.01 in ² (2.08...5.26 mm ²) AWG 14...AWG 10) 5.08 N.m (45 lbf.in) 0.01 in ² (8.37 mm ²) AWG 8) 5.08 N.m (45 lbf.in) 0.02...0.03 in ² (12.3...21.12 mm ²) AWG 6...AWG 4) 5.65 N.m (50 lbf.in) 0.04 in ² (26.67 mm ²) AWG 3)

Ordering and shipping details

Category	00006 - D & DU SW, NEMA1, 30-200A
Discount Schedule	DE1A

GTIN	00785901461234
Package weight(Lbs)	3.60 kg (7.93 lb(US))
Returnability	Yes
Country of origin	US

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds which is known to the State of California to cause Carcinogen & Reproductive harm. For more information go to www.p65warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------