

Product data sheet

Characteristics

DU321

SWITCH NOT FUSIBLE GD 240V 30A 3P

NEMA1

Product availability : Stock - Normally stocked in distribution facility



Price** : 155.00 USD



Main

Product	Single Throw Safety Switch
Current Rating	30 A
Certifications	UL listed file E2875
Enclosure Rating	NEMA 1
Disconnect Type	Non-fusible disconnect switch
Factory Installed Neutral	None
Mounting Type	Surface
Number of Poles	3
Electrical Connection	Lugs
Duty Rating	General duty
Voltage Rating	240 V AC
Wire Size	AWG 14...AWG 6 copper AWG 12...AWG 6 aluminium

Complementary

Width	184.15 mm (7.25 in)
Height	234.95 mm (9.25 in)
Depth	92.20 mm (3.63 in)
Tightening torque	3.39 N.m (30 lbf.in) 0.00...0.02 in ² (2.08...13.3 mm ²) AWG 14...AWG 6

Ordering and shipping details

Category	00006 - D & DU SW, NEMA1, 30-200A
Discount Schedule	DE1A
GTIN	00785901491606
Package weight(Lbs)	1.93 kg (4.25 lb(US))
Returnability	Yes

Country of origin	MX
-------------------	----

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds which is known to the State of California to cause Carcinogen & Reproductive harm. For more information go to www.p65warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------