

Product availability : Stock - Normally stocked in distribution facility



Price** : 18,114.00 USD



Main

Product	Single Throw Safety Switch
Current Rating	1200 A
Certifications	UL listed file E2875
Enclosure Rating	NEMA 1 steel
Factory Installed Neutral	Neutral (factory installed)
Disconnect Type	Fusible disconnect
Short Circuit Current Rating	200 kA maximum L
Mounting Type	Surface
Number of Poles	3
Electrical Connection	Lugs
Duty Rating	Heavy duty
Voltage Rating	600 V AC/DC
Wire Size	AWG 3/0...750 kcmil copper or aluminium

Complementary

Width	930.15 mm (36.62 in)
Height	1755.90 mm (69.13 in)
Depth	450.85 mm (17.75 in)
Tightening torque	42.37 N.m (375 lbf.in) 0.13...0.59 in ² (85.01...380 mm ²) AWG 3/0...750 kcmil)

Ordering and shipping details

Category	00053 - H&HU SW,NEMA1,400-1200A
Discount Schedule	DE1
GTIN	00785901442462
Package weight(Lbs)	164.20 kg (362 lb(US))
Returnability	Yes
Country of origin	MX

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------