

Product data sheet

Characteristics

HDL36080

Circuit breaker, PowerPact H, thermal magnetic, 80A, 3 pole, 600V, 14kA

Product availability : Stock - Normally stocked in distribution facility



Price* : 1,328.00 USD



Main

Product or component type	Circuit breaker
Range of product	PowerPact H
Trip Unit Type	Thermal-magnetic
Breaking capacity code	D

Complementary

Line Rated Current	80 A
Number of Poles	3P
Interrupt Rating	25 kA 240 V AC 18 kA 480 V AC 14 kA 600 V AC 20 kA 250 V DC
[Ue] rated operational voltage	250 V DC 600 V AC
Continuous current rating	80 %
Mounting mode	Unit mount
Electrical connection	Lugs load Lugs line
Wire Gauge	AWG 14...AWG 3/0 aluminium/copper
Magnetic hold current	800 A
Magnetic tripping current	1450 A
Height	6.4 in (162.56 mm)
Width	4.12 in (104.65 mm)
Maximum Depth	4.36 in (110.74 mm)
Tightening torque	44.25 lbf.in (5 N.m) 0.00...0.15 in ² (2.5...95 mm ²) AWG 14...AWG 3/0)

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Aug 18, 2020

Environment

Product certifications	CSA UL Listed CE IEC
Ambient air temperature for operation	104 °F (40 °C)

Ordering and shipping details

Category	01110 - HD,JD UNIT MT BREAKER/SWITCH
Discount Schedule	DE2
GTIN	00785901623168
Nbr. of units in pkg.	1
Package weight(Lbs)	4.1 lb(US) (1.86 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	7.30 in (18.542 cm)
Package 1 width	6.40 in (16.256 cm)
Package 1 Length	8.80 in (22.352 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------

Approximate Dimensions

