

Product data sheet

Characteristics

HEPD80

SPD, HEPD type 1, 120/240 V, 1 PH, 3 wire, 80 kA

Product availability : Stock - Normally stocked in distribution facility



Price** : 185.00 USD



Main

Product	Surge protection device
Surge Arrester Type	Electrical distribution network
Range	Square D
Device Short Name	HEPD
Accessory Category	Mounting accessory

Complementary

Surge Current	80 kA per phase
Voltage Rating	120/240 V AC
Number of Phases	1 phase
Wiring Configuration	3-wire (isolated ground)
Connection	Wire AWG 14
MCOV	150 V
Nominal Discharge Current	10 kA
Rated Current	10 kA
SCCR	25 kA
Local Signalling	1 LED green normal operation 1 LED green off
Mounting Location	Side
Mounting Support	Bracket
Product destination	Load center
Input voltage	600 V L-N 600 V L - G 1000 V L - L 900 V N - G
Height	3.23 in (82.04 mm)
Width	3.72 in (94.49 mm)

Depth	2.10 in (53.34 mm)
Cable length	34 in (863.60 mm)

Environment

Enclosure Rating	NEMA 4X
Enclosure Material	non-metallic
Standards	UL 1449 CUL UL 1449:ed. 4 type I
Ambient Operating	-40...149 °F (-40...65 °C)

Ordering and shipping details

Category	08461 - SURGE PROTECTION RESI
Discount Schedule	DE1B
GTIN	00785901008729
Returnability	Yes
Country of origin	US

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.

Contractual warranty

Warranty	18 months
----------	-----------

Approximate Dimensions

