

Product availability : Stock - Normally stocked in distribution facility



Price** : 404.00 USD



Main

Product	Miniature circuit-breaker
Range	Homeline
Current Rating	200 A
Certifications	UL listed
Voltage Rating	120/240 V AC
Mounting Type	Plug-in
Number of Poles	2P
Short Circuit Current Rating	10 kA
Number of Spaces	2
Circuit Breaker Type	Standard
Ratings	HACR rated
Electrical Connection	Box lugs
Wire Size	AWG 4...300 kcmil aluminium/copper)1

Complementary

Tightening torque	42.48 lbf.in (4.8 N.m) AWG 4...300 kcmil)
-------------------	---

Environment

Ambient air temperature for operation	104 °F (40 °C)
---------------------------------------	----------------

Ordering and shipping details

Category	00151 - HOM MAIN BREAKERS
Discount Schedule	DE3D
GTIN	00785901065883
Package weight(Lbs)	0.80 kg (1.76 lb(US))
Returnability	Yes

Country of origin	MX
-------------------	----

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	Lifetime
----------	----------