

Product data sheet

Characteristics

HOMT2020240

Tandem miniature circuit breaker, Homeline, 2 x 1 pole at 20A, 1 x 2 pole at 40A, 120/240 VAC, 10 kA AIR, plug in

Product availability : Stock - Normally stocked in distribution facility



Price** : 120.00 USD



Main

Product	Miniature circuit-breaker
Range	Homeline
Current Rating	20 A 40 A
Certifications	UL listed
Voltage Rating	120/240 V AC
Mounting Type	Plug-in
Number of Poles	2P 1P
Short Circuit Current Rating	10 kA
Number of Spaces	2
Circuit Breaker Type	Quad tandem
Ratings	HACR rated
Electrical Connection	Box lugs
Wire Size	AWG 14...AWG 6 copper)1 AWG 12...AWG 6 aluminium)1 AWG 12...AWG 8 aluminium)1

Complementary

Height	3.13 in (79.50 mm)
Width	2 in (50.80 mm)
Depth	2.98 in (75.69 mm)
Tightening torque	35.40 lbf.in (4.0 N.m) 0.00...0.02 in ² (2.5...10 mm ²) AWG 16...AWG 14) 35.40 lbf.in (4.0 N.m) 0.01...0.03 in ² (4...20 mm ²) AWG 12...AWG 4)

Environment

Ambient air temperature for operation	104 °F (40 °C)
---------------------------------------	----------------

Ordering and shipping details

Category	00046 - HOM/T 15-30A 1P; 15-60A 2P
Discount Schedule	DE3D
GTIN	00785901377047
Returnability	Yes
Country of origin	MX

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	Lifetime
----------	----------