

Product data sheet

Characteristics

HU362AWC

Safety switch, heavy duty, non fusible, 60A, 600 VAC/VDC, 3 poles, 60 hp, NEMA 12K, crouse hinds arktite

Product availability : Stock - Normally stocked in distribution facility



Price* : 2,678.00 USD



Main

Product	Receptacle Switch
For Use With	Plug APJ6485 Crouse-Hinds Arktite
Current Rating	60 A
Enclosure Rating	NEMA 3R/12 galvanized steel
Horsepower Rating	50 hp 480 V AC 50...60 Hz 3 phase NEC 430.52 60 hp 600 V AC 50...60 Hz 3 phase NEC 430.52 10 hp 250 V DC NEC 430.52
Disconnect Type	Non-fusible disconnect switch
Short Circuit Current Rating	200 kA
Mounting Type	Surface
Number of Poles	3
Phase	3 phase
Electrical Connection	Receptacle
Certifications	UL Listed
Voltage Rating	600 V AC 250 V DC
Wire Size	AWG 12...AWG 2 aluminium AWG 14...AWG 2 copper
Wire Configuration	4-wire

Complementary

Short-circuit withstand	200 kA
Maximum Width	10.5 in (266.70 mm)
Maximum Height	16.5 in (419.10 mm)
Maximum Depth	7 in (177.80 mm)

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Tightening torque	45 lbf.in (5.08 N.m) AWG 6...AWG 4) 40 lbf.in (4.52 N.m) AWG 8) 35 lbf.in (3.95 N.m) AWG 14...AWG 10)
-------------------	---

Ordering and shipping details

Category	00118 - H&HU SW,W/C-HINDS RECPT-WC
Discount Schedule	DE1
GTIN	00785901195634
Nbr. of units in pkg.	1
Package weight(Lbs)	24.03 lb(US) (10.90 kg)
Returnability	Yes
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	9.40 in (23.876 cm)
Package 1 width	12.00 in (30.48 cm)
Package 1 Length	27.70 in (70.358 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------