

JDL36200

PowerPact J-Frame breaker, thermal-magnetic,
200 A, 3P, 14 kA at 600 VAC

Product availability : Stock - Normally stocked in distribution facility



Price** : 2,730.00 USD



Main

Product or component type	Circuit breaker
Range of product	PowerPact J
Trip unit technology	Thermal-magnetic
Breaking capacity code	D

Complementary

Line Rated Current	200 A
Number of poles	3
Poles description	3P
Breaking capacity	25 kA 240 V AC 18 kA 480 V AC 14 kA 600 V AC 20 kA 250 V DC
[Ue] rated operational voltage	600 V AC 250 V DC
Continuous current rating	80 %
Mounting mode	Unit mount
Electrical connection	Lugs load Lugs line
AWG gauge	AWG 3/0...350 kcmil aluminium/copper
Magnetic hold current	1000 A
Magnetic tripping current	2000 A
Height	7.52 in (191.01 mm)
Width	4.12 in (104.65 mm)
Depth	5 in (127.00 mm)
Tightening torque	230.12 lbf.in (26 N.m) 0.15...0.29 in ² (95...185 mm ²) AWG 3/0...350 kcmil)

Environment

Product certifications	IEC CSA CE UL listed CCC
Ambient air temperature for operation	104 °F (40 °C)

Ordering and shipping details

Category	01110 - HD,JD UNIT MT BREAKER/SWITCH
Discount Schedule	DE2
GTIN	00785901955856
Returnability	Yes
Country of origin	MX

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------

Approximate Dimensions

