



Price* : 6,002.00 USD



Main

Product or component type	Circuit breaker
Range of product	PowerPact J
Trip unit technology	Thermal-magnetic
Breaking capacity code	G

Complementary

Line Rated Current	250 A
Number of poles	3
Poles description	3P
Breaking capacity	20 kA 500 V DC 20 kA 250 V DC 65 kA 240 V AC 35 kA 480 V AC 18 kA 600 V AC
[Ue] rated operational voltage	500 V DC 600 V AC
Continuous current rating	100 %
Mounting mode	Unit mount
Electrical connection	Lugs load Lugs line
AWG gauge	AWG 3/0...350 kcmil aluminium/copper
Magnetic hold current	1250 A
Magnetic tripping current	2500 A
Maximum Height	7.52 in (191.01 mm)
Maximum Width	4.12 in (104.65 mm)
Maximum Depth	5 in (127.00 mm)
Tightening torque	230.12 lbf.in (26 N.m) 0.15...0.29 in ² (95...185 mm ²) AWG 3/0...350 kcmil)

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Environment

Product certifications	CCC CE IEC UL Listed CSA
Ambient air temperature for operation	104 °F (40 °C)

Ordering and shipping details

Category	01115-HG,HJ,JG,JJ UNIT MT BREAKER/SWITCH
Discount Schedule	DE2
GTIN	00785901552390
Nbr. of units in pkg.	1
Package weight(Lbs)	6.00 lb(US) (2.722 kg)
Returnability	Yes
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	5.13 in (13.018 cm)
Package 1 width	7.25 in (18.415 cm)
Package 1 Length	8.44 in (21.433 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------