



Main

Range	TeSys
Device short name	LA4D
Product or component type	Suppressor module
Product compatibility	3P LC1D80...D150 4P LC1D80004...D115004 4P LC1D40008...D80008

Complementary

Mounting location	Top
Mounting mode	By screws
Suppressor technology	RC circuit
[Uc] control circuit voltage	24...48 V AC 50/60 Hz
Maximum peak voltage	3 Uc
Net weight	0.018 kg

Environment

Ambient air temperature for operation	-25...55 °C
Ambient air temperature for storage	-40...80 °C

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes

RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------