



Main

Range of product	TeSys U
Device short name	LUA1
Product or component type	Auxiliary contact

Complementary

Auxiliary contact composition	1 NO + 1 NC
Signalling function	Fault signalling Indicating rotary knob inready position
[Ue] rated operational voltage	≤ 250 V AC ≤ 250 V DC
[Ui] rated insulation voltage	250 V conforming to CSA 250 V conforming to IEC 60947-5-1 250 V conforming to UL
[Ith] conventional free air thermal current	5 A
Minimum switching voltage	17 V
Minimum switching current	5 mA
Product weight	0.03 kg
Connections - terminals	Screw clamp terminals

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.