

Product data sheet

Characteristics

MD3304X

Motor disconnect switch, 3 P, 30 A, NEMA 1, 3, 3R, 4, 4X and 12 enclosure

Product availability : Stock - Normally stocked in distribution facility



Price** : 124.60 USD



Main

Range	MD
Product	Motor Disconnect Switch
Current Rating	30 A
Horsepower Rating	7.5 hp 220/240 V AC 20 hp 440/480 V AC 25 hp 600 V AC
Enclosure Rating	NEMA 4X
Certifications	UL listed

Ordering and shipping details

Category	21730 - V VARIO SWITCH
Discount Schedule	CP1
GTIN	00785901871712
Returnability	Yes
Country of origin	CN

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------

Approximate Dimensions

