

Product data sheet

Characteristics

NQ442L4C

NQ Pnlbrd Interior 400A, 3 PH, 4 Wire, 42 CCT,
Mn Lug, Cu

Product availability : Stock - Normally stocked in distribution facility



Price* : 2,133.00 USD



Main

Load center type	Main lugs
Branch Circuit Breaker Type	QHB QOB QOB-VH
Connections - terminals	Lug line AWG 1/0...750 kcmil aluminium Lug neutral AWG 1/0...750 kcmil aluminium
Busbar Material	Copper

Complementary

Number of spaces	42
Enclosure Nominal Height	50 in
Enclosure Nominal Width	20 in
Enclosure Nominal Width	5.75 inFor NEMA 1 enclosure 6.5 inFor NEMA 3R/5/12 enclosure
Line Rated Current	400 A
Wiring configuration	4-wire
Phase	3 phases
System Voltage	240 V AC 48 V DC
Tightening torque	31.07...33.9 N.m 53.48...380 mm ² (AWG 1/0...750 kcmil) 31.07...33.9 N.m 53.48...177.3 mm ² (AWG 1/0...350 kcmil) 62.14 N.m 53.48...380 mm ² (AWG 1/0...750 kcmil) 62.14 N.m 53.48...152 mm ² (AWG 1/0...300 kcmil) 42.37 N.m 53.48...380 mm ² (AWG 1/0...750 kcmil) 42.37 N.m 53.48...152 mm ² (AWG 1/0...300 kcmil)


Environment

Standards	UL CSA
-----------	-----------

Ordering and shipping details

Category	09151 - NQ RTA PANELBOARDS
Discount Schedule	PE1A
GTIN	00785901507918
Nbr. of units in pkg.	1
Package weight(Lbs)	21.75
Returnability	Y
Country of origin	MX

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1419 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Nickel compounds which is known to the State of California to cause cancer and
- - - - - Substance 2	Bisphenol A (BPA) which is known to the State of California to cause birth defects or other reproductive harm.
- - - - - More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------