

Product data sheet

Characteristics

NSYCCOTHDF

ClimaSys CC - double thermostat 250V - range of temperature 0...60°C - 1NO/NC - °F

Product availability : Stock - Normally stocked in distribution facility

Price** : 41.25 USD



Main

Range	ClimaSys
Product name	ClimaSys CC
Product or component type	Double thermostat
Temperature setting range	32...140 °F (0...60 °C)
Information displayed	Temperature in °F

Complementary

Input voltage	250 V
Sensor type	Bimetal
Contacts type and composition	1 NO/NC
Contact resistance	10 mOhm
Service life in cycles	100000 cycles
Maximum switching capacity	2 A 120...250 V AC inductive 0.6 10 A 250 V AC resistive 15 A 120 V AC resistive 30 W DC
Electrical connection	4 terminals 2.5 mm ²
Mounting mode	Clipped
Height	External 2.68 in (68 mm)
Width	External 2.20 in (56 mm)
Depth	External 1.73 in (44 mm)
Product weight	1.41 oz (40 g)
Mounting location	On mounting plate 35 mm DIN rail Spacial upright Cross rails
Ambient air temperature for operation	-4...176 °F (-20...80 °C)
IP degree of protection	IP20
Hysteresis	7 %
Number of outputs	1 heating function 1 ventilation function
Material	PC

Color	Light grey
Flame retardance	Self-extinguishing UL94 (material V0)
Product certifications	UL

Ordering and shipping details

Category	80034 - ENCLOSURE SYSTEMS WALL MOUNT METAL
Discount Schedule	ES1
GTIN	00785901978091
Package weight(Lbs)	0.10 kg (0.23 lb(US))
Returnability	Yes
Country of origin	CN

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals which are known to the State of California to cause Carcinogen & Reproductive harm. For more information go to www.p65warnings.ca.gov
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.

Contractual warranty

Warranty	18 months
----------	-----------