



Main

Range	ClimaSys
Product name	ClimaSys CR
Product or component type	Resistance heater
Rated power in W	20 W
Input voltage	110...250 V AC 50/60 Hz
Electrical connection	4 screw terminals 2.5 mm ²

Complementary

Operating position	Vertical
Ambient air temperature for operation	-40...70 °C
IP degree of protection	IP20
Electrical insulation class	Class II
Product certifications	UL VDE
Material	Extruded aluminium for body Plastic for cover
Height	External : 98 mm
Width	External : 38 mm
Depth	External : 75 mm
Condition of use	Air sealed enclosure Electrical protection is needed Heaters must be installed with a thermal controller
Fixing mode	By clips
Mounting support	35 mm DIN rail

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS (date code: YYWW)	Compliant - since 0940 - Schneider Electric declaration of conformity

REACH

Reference not containing SVHC above the threshold
Reference not containing SVHC above the threshold

Contractual warranty

Warranty period

18 months