

# Product data sheet

## Characteristics

# NSYCRN86250

Spacial CRN plain door w/o mount.plate.  
H800xW600xD250 IP66 IK10 RAL7035..



### Main

Range of product	Spacial CRN
Application	Multi-purpose
Category	Compact enclosure
Enclosure nominal height	800 mm
Enclosure nominal width	600 mm
Enclosure nominal depth	250 mm
Installation accessory type	Wall-mounting
Device composition	Lock 1 Door 1 Cable gland plate 1 Body 1
Door type	Plain
Mounting plate description	Without mounting plate

### Complementary

Body type	Sides made from a single folded section Back welded with double profile forming a protected sealed area
Number of doors	1 front face
Door opening	Reversible 120 °
Lock type	3 mm double-bar lock
Type of gland plate	Standard
Accessibility for operation	Front
Removable parts	Cable gland plate by screws Door by hinges
Material	Steel for body
Surface finish	Epoxy-polyester powder
Colour	Grey RAL 7035
Standards	IEC 62208
Product certifications	CUL UL

### Environment

IP degree of protection	IP66 conforming to IEC 60529
IK degree of protection	IK10 conforming to IEC 62262

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0940 -  Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available  Download Product Environmental
Product end of life instructions	Need no specific recycling operations