Product data sheet Characteristics

NSYPTDS2

Spacial - Flush Mounting drive installation kit - Altivar Process size S2 - IP55



Main

Range	Spacial
Product or component type	Drive flush mounting kit
Accessory / separate part category	Mounting and fixing accessory
Product specific application	Process and utilities
Range compatibility	Spacial SF and SM enclosures: H:>=500 mm x W:>=300 mm Spacial S3D enclosure: H:>=500 mm x W:>=300 mm Altivar variable speed drive ATV630 Altivar variable speed drive ATV930
NEMA size	2
Mounting location	Mode 2 : inside enclosure Mode 1 : back of enclosure on mounting plate
Kit composition	1 x mounting plate with flanges and integrated gasket, steel with anti-corrosive coating. Fixing by screws and nuts 1 x fixing accessories 1 x drilling template 1 x instruction sheet 1 x edge protector profile, plastic.

Complementary

Permanent permissible load	7.7 kg	;
Colour	Grey RAL 7035	<u> </u>
Height	External : 420 mm Cut-out : 375 mm	:
Width	External : 265 mm Cut-out : 215 mm	
Depth	Wall-enclosure separation : 22 mm	
Product weight	1.7 kg	
Services	Configuration of enclosure pre-drilled back at requested dimensions Factory installation drive flush mounting kit on enclosure	- - -

Environment

Environment		
IP degree of protection	IP55 conforming to IEC 60529	
Offer Sustainability		
Sustainable offer status	Not Green Premium product	
RoHS (date code: YYWW)	Compliant - since 1602 - Schneider Electric declaration of conformity	
	Schneider Electric declaration of conformity	
REACh	Reference not containing SVHC above the threshold	
	Reference not containing SVHC above the threshold	