

PL100WS2M1

LIMIT SWITCH



List Price \$410.00 USD

Availability **Non-Stock Item: This item is not normally stocked in our distribution facility.**

Technical Characteristics

Enclosure Rating	NEMA 1/4/13
Features	Metal Front Cover
Head Type	Rotary
Mounting Type	Panel
Function	Two Circuit - Single Operation
Operating Temperature Range	0 to 200 Degrees F
Type	L100
Type of Duty	Severe Duty (Mill)
Vibration Resistance	30G (10-55Hz)
Wire Size	(1) #12AWG or (2) #14AWG
Actuator Action	Momentary
Operating Torque/Force	190 Inch-Ounces
Approvals	UL Listed File Number 42259 CCN NKCR - CSA Certified File Number LR25490 - Class 3211-03 - CE Marked
Body Material	Cast Aluminum
Connection Type	4 Pin (Male) APL/PL-SWTS (Cannon# MS3102E20-4P-F79 or equal)
Contact Operation	Snap Action
Contact Material	Silver Alloy
Contact Rating	NEMA A600/P600
Contact Form	2-Pole Double Break (Isolated Contacts)
Terminal Type	Screw Clamp
Ampere Rating	20A
Maximum Voltage Rating	600V

Shipping and Ordering

Category	22426 - Limit Switches, Heavy Duty, Mill & Foundry, Type L
Discount Schedule	T
GTIN	00785901171805
Package Quantity	1
Weight	1.65 lbs.
Availability Code	Non-Stock Item: This item is not normally stocked in our distribution facility.
Returnability	N
Country of Origin	MX

Generated: 08/24/2011 10:00:44