

Product data sheet

Characteristics

QO120GFI

Mini CB, QO, 20 A, 1P, 120 V, 10 kA, Plug in, GFI

Product availability : Stock - Normally stocked in distribution facility



Price* : 233.00 USD



Main

Product	Miniature circuit-breaker
Range	QO
Line Rated Current	20 A
System Voltage	120 V AC
Mounting Type	Plug-in
Number of Poles	1P
Circuit Breaker Type	Ground fault protecting class A 6 mA
Ratings	Not rated
Electrical Connection	Pressure plate

Complementary

Interrupt Rating	10 kA at: 120 V AC 50/60 Hz
Number of Panel Spaces	1
Wire Size	AWG 14...AWG 8 (copper) AWG 12...AWG 8 (aluminium)
Height	4.12 in
Depth	2.91 in
Width	0.75 in

Environment

Certifications	CSA UL listed
Ambient Rating	104 °F (40 °C)

Ordering and shipping details

Category	00003 - QO 1&2 POLE GFI CB 30A MAX
Discount Schedule	DE2A

GTIN	00785901255079
Nbr. of units in pkg.	1
Package weight(Lbs)	0.530000000000000003
Returnability	Y
Country of origin	MX

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1340 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity
REACH	Reference contains SVHC above the threshold - Go to CaP for more details  Go to CaP for more details
Product environmental profile	Available
Product end of life instructions	Available
California proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------