

Product data sheet

Characteristics

QO1515

Mini CB, QO Tandem, 15 A, 1P, 120/240 V, 10 kA, Plug in

Product availability : Stock - Normally stocked in distribution facility



Price** : 73.00 USD



Main

Product	Miniature circuit-breaker
Range	QO
Current Rating	15 A
Voltage Rating	120/240 V AC
Mounting Type	Plug-in
Number of Poles	1P
Circuit Breaker Type	Tandem
Ratings	HACR rated
Electrical Connection	Box lugs

Complementary

Interrupt Rating	10 kA 120/240 V AC 50/60 Hz
Number of Panel Spaces	1
Wire Size	AWG 14...AWG 8 copper or aluminium
Tightening torque	40.71 lbf.in (4.6 N.m)
Height	81.79 mm (3.22 in)
Depth	73.91 mm (2.91 in)
Width	19.05 mm (0.75 in)

Environment

Certifications	UL listed CSA
Ambient Rating	104 °F (40 °C)

Ordering and shipping details

Category	00181 - REPLCMNT TANDEMS - DO NOT NEGOTIATE
Discount Schedule	DE2A
GTIN	00785901400905
Package weight(Lbs)	0.15 kg (0.32 lb(US))
Returnability	Yes
Country of origin	MX

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
Halogen content performance	Halogen free product

Contractual warranty

Warranty	18 months
----------	-----------