

Product data sheet

Characteristics

QO215CP

QO Miniature Circuit Breaker 15A 2P 120/240V 10kA Plug-in Mount

Product availability : Stock - Normally stocked in distribution facility



Main

Product or component type	Miniature circuit-breaker
Range of product	QO
Line Rated Current	15 A
System Voltage	120/240 V AC 48 V DC
Mounting mode	Plug-in
Poles description	2P
Circuit breaker type	Standard
Circuit breaker application	HACR rated
Electrical connection	Pressure plate
Type of packing	Consumer packaging

Complementary

Breaking capacity	10 kA at: 120/240 V AC 5 kA at: 48 V DC
Number of spaces required	2
AWG gauge	AWG 14...AWG 8 (copper or aluminium)
Height	3 in
Depth	2.91 in
Width	1.5 in

Environment

Product certifications	CSA UL listed
Ambient air temperature for operation	104 °F (40 °C)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ordering and shipping details

Category	01341 - QO 2 POLE BULK BRKRS15-60A
Discount Schedule	CPQ
GTIN	00047569008948
Nbr. of units in pkg.	5
Package weight(Lbs)	0.5300000000000003
Returnability	Y
Country of origin	MX

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1323 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations