

Product availability : Stock - Normally stocked in distribution facility



Price\* : 113.00 USD



## Main

Product	Load Center
Marketing Trade Name	QO
Load center type	Main lugs
Line Rated Current	40 A
Number of spaces	2
Short Circuit Current Rating	65 kA
Maximum Number of Single Pole Circuits	2
Maximum Number of Tandem Breakers	0
Phase	1 phase
System Voltage	120/240 V AC

## Complementary


Wire Size	AWG 14...AWG 6 (copper) AWG 12...AWG 6 (aluminium)
Enclosure Rating	NEMA 3R outdoor
Cover type	Surface cover
Electrical Connection	Lugs
Grounding Bar	Grounding bar (ordered separately)
Electrical connection	Lugs
Wiring configuration	3-wire
Busbar Material	Tin plated aluminium busbar
Enclosure Material	Welded galvanized steel
Cover Finish	Baked enamel grey
Box number	1R
Product certifications	UL listed
Height	9.37 in (238 mm)

Width	4.88 in (124 mm)
-------	------------------

## Ordering and shipping details

Category	00101 - QO 1PH LC,2-8CKT,NEMA 1,3R
Discount Schedule	DE3A
GTIN	00785901785118
Nbr. of units in pkg.	1
Package weight(Lbs)	4.9900000000000002
Returnability	Y
Country of origin	MX

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant  <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Lead and lead compounds which is known to the State of California to cause cancer and birth defects or other reproductive harm.
- - - - - More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

## Contractual warranty

Warranty period	18 months
-----------------	-----------