

QOB350

Miniature Circuit Breaker (QOB) Standard, 50A,
3-Pole, 240 Vac, 3-Phase, Bolt-On



by Schneider Electric

List Price \$293.00 USD

Availability **Stock Item: This item is normally stocked in our distribution facility.**

Technical Characteristics

Approvals	UL Listed - CSA Certified
Features	VISI-TRIP trip indication
Circuit Breaker Type	Standard
For Use With	NQ & NQOD Panelboards/Interiors
Marketing Trade Name	QO
Mounting Type	Bolt-On
HACR Rated	Yes
Voltage Rating	240 Vac
Space Required	3
Number of Poles	3-Pole
Short Circuit Current Rating	10kA
Phase	3-Phase
Type	QOB
Terminal Type	Box Lugs
Ampere Rating	50A
General Application	Provides overload and short circuit protection
Wire Size	#8 to #2 AWG(Al/Cu)

Shipping and Ordering

Category	00015 - Circuit Breakers, 1 Pole: 10 - 70 Amp, 2 Pole: 10 - 125 Amp, 3 Pole: 10 -160 Amp, Type QO
Discount Schedule	DE2
GTIN	00785901417163
Package Quantity	1
Weight	0.83 lbs.
Availability Code	Stock Item: This item is normally stocked in our distribution facility.
Returnability	Y
Country of Origin	MX

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.

Generated: 01/24/2013 02:27:45