

# Product data sheet

## Characteristics

# QOB3150VH

Mini circuit breaker, QO, 150A, 3 pole, 120/240 VAC, 22 kA, bolt on mount

Product availability : Stock - Normally stocked in distribution facility



Price\* : 1,809.00 USD



### Main

Product	Miniature circuit-breaker
Range	QO
Current Rating	150 A
Voltage Rating	120/240 V AC 240 V AC 120 V AC
Mounting Type	Bolt-on
Number of Poles	3P
Circuit Breaker Type	Standard
Ratings	Not rated
Electrical Connection	Box lugs

### Complementary

Interrupt Rating	22 kA 120/240 V AC 50/60 Hz 22 kA 240 V AC 50/60 Hz 22 kA 120 V AC 50/60 Hz
Number of Panel Spaces	6
Wire Size	AWG 4...300 kcmil copper or aluminium
Tightening torque	40.71 lbf.in (4.6 N.m)
Height	5.72 in (145.29 mm)
Maximum Depth	4.9 in (124.46 mm)
Maximum Width	4.5 in (114.30 mm)

### Environment

Certifications	UL Listed CSA
----------------	------------------

\* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ambient Rating	104 °F (40 °C)
----------------	----------------

## Ordering and shipping details

Category	00015 - QOB CIRCUIT BREAKERS
Discount Schedule	DE2
GTIN	00785901065517
Nbr. of units in pkg.	1
Package weight(Lbs)	3.94 lb(US) (1.79 kg)
Returnability	Yes
Country of origin	MX

## Packing Units

Unit Type of Package 1	PCE
Package 1 Height	4.30 in (10.922 cm)
Package 1 width	5.00 in (12.7 cm)
Package 1 Length	6.70 in (17.018 cm)
Unit Type of Package 2	PAL
Number of Units in Package 2	558
Package 2 Weight	2199.00 lb(US) (997.449 kg)
Package 2 Height	40.00 in (101.6 cm)
Package 2 width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
RECh Regulation	<a href="#">RECh Declaration</a>
RECh free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Halogen content performance	Halogen free product

## Contractual warranty

Warranty	18 months
----------	-----------

Approximate Dimensions

